

Frascold SA 3 13 D Y/2 condensing unit

Specifications

Marque	Frascold
Le type	SA 3 13 D Y/2 condensing unit
Réfrigérant	Freon
kW at +10°C/+40°C	10.29
kW at 0°C/+40°C	9
kW at -5°C/+40°C	7.73
kW at -10°C/+40°C	6.61
kW at -20°C/+40°C	4.61
kW at -30°C/+40°C	2.94
Interrupteurs de sécurité de pression	✓
Séparateur d'huile	✓
Liquid déshydrateur ligne	✓
m3 / h	1384
Remarques	Our capacity table is based on Manufacturer spec. We would like to know which refrigerant is in your system
Remarques	temperature is at +10°C/+32°C // 0°C/+32°C etc
Remarques	fan 0.145 kW at 1400 RPM
Condensing Unit	✓



Tailles	1110x630x780mm (LxWxH)
Stock	1

Description

Used Frascold SA 3 13 D Y/2 condensing unit

Used Frascold condensing unit type SA 3 13 D Y/2 semi hermetic reciprocating compressor , with 2 fans 0.145 kW at 1400 RPM and consisting components (see picture). "*Why choose for HOSBV? Were not only the largest used refrigeration specialist in Europe, but also, we deliver all equipment including an extensive test, warranty and industrial cleaning. Optional we can arrange shipment and export documents."



Model	pk	Omkasting <i>[optioneel]</i>	Koelvermogen in kW bij $t_{\text{omg}} = 32^{\circ}\text{C}$ en t_{d}						
			+5 °C	0°C	-5°C	-10°C	-20°C	-30°C	
SA 0.5 4 A Y ¹⁾	<input type="checkbox"/>	0,5	USHOU5	2,88	2,53	2,21	1,91	1,34	0,85
SA 0.5 5 A Y	<input type="checkbox"/>	0,5	USHOU5	—	—	2,52	2,19	1,57	1,01
SA 0.7 5 A Y ¹⁾	<input checked="" type="checkbox"/>	0,75	USHOU5	—	—	3,38	2,91	2,48	1,70
SA 0.7 6 A Y	<input type="checkbox"/>	0,75	USHOU5	—	—	—	—	2,33	1,69
SA 1.6 A Y ¹⁾	<input checked="" type="checkbox"/>	1	USHOU5	4,2	3,67	3,15	2,70	1,86	1,18
SA 1.7 A Y ¹⁾	<input checked="" type="checkbox"/>	1	USHOU5	—	—	—	—	3,18	2,25
SA 1.5 7 A Y ¹⁾	<input checked="" type="checkbox"/>	1,5	USHOU6	5,76	4,99	4,27	3,62	2,45	1,54
SA 1.5 9 B Y ¹⁾	<input checked="" type="checkbox"/>	1,5	USHOU5	—	—	4,42	3,83	2,74	1,81
SA 2.10 B Y ¹⁾	<input checked="" type="checkbox"/>	2	USHOU6	—	—	6,54	5,67	4,87	3,41
SA 2.11 D Y	<input type="checkbox"/>	2	USHOU6	—	—	6,91	6,01	5,20	3,68
SA 2.11 D/2 Y	<input checked="" type="checkbox"/>	2	USHOU7	9,02	7,84	6,70	5,71	3,92	2,50
SA 2.13 D Y	<input checked="" type="checkbox"/>	2	USHOU6	—	—	5,93	5,08	4,29	2,82
SA 2.13 D/2 Y	<input checked="" type="checkbox"/>	2	USHOU7	—	—	—	—	6,64	4,65
SA 3.13 D Y	<input checked="" type="checkbox"/>	3	USHOU6	8,65	7,73	6,81	5,91	4,24	2,77
SA 3.13D/2 Y	<input checked="" type="checkbox"/>	3	USHOU7	10,29	9,00	7,73	6,61	4,61	2,94
SA 2.15 D Y	<input checked="" type="checkbox"/>	2	USHOU6	—	—	—	—	4,69	3,21
SA 3.15 D Y	<input type="checkbox"/>	3	USHOU6	—	—	8,22	7,34	6,37	4,62
SA 4.16 D/2 Y	<input checked="" type="checkbox"/>	4	USHOU7	12,58	11,01	9,54	8,19	5,75	3,78
SA 4.16 F/2 Y	<input type="checkbox"/>	4	USHOU7	12,7	11,11	9,62	8,24	5,75	3,76
SA 3.18 D Y	<input checked="" type="checkbox"/>	3	USHOU6	—	—	—	—	7,11	5,30
SA 3.18 D/2 Y	<input checked="" type="checkbox"/>	3	USHOU7	—	—	9,49	8,25	5,93	3,96
SA 4.18 D/2 Y	<input type="checkbox"/>	4	USHOU7	—	—	11,72	10,16	8,74	6,20